



# Perasteril

## Airborne Disinfectant for Surfaces & Environment

Broad spectrum disinfection efficacy  
**(Bactericidal, Fungicidal, Virucidal & Sporicidal)**  
on pre cleaned surfaces.

**Perasteril** is best used with airborne disinfection devices, which diffuses it into Hydrogen peroxide vapor.



**Bio decontamination treatment of aseptic areas, sterile areas within 60 minutes.**

**Offers microbiologically validated treatment**

**Ecological, Colorless**

**Leaves no visible residues, Biodegradable to non-toxic elements.**

**Free of Aldehydes, Quats, Chlorine, Non Carcinogenic.**

**Perasteril +**  
Airborne disinfection devices

**SATEJ 3D i**

**SATEJ PLUS i**

**TRS 01**

**YANTRA**

**AEROJET Steriz**



**Highly effective &  
Automated treatment with  
diffusion time calculated as  
per room size**

**Airborne Disinfection Treatment Dosage:**

Room Space	Dilution	Total solution required
1000cuft	100ml Perasteril + 100ml of DM water	200ml
2000cuft	200ml Perasteril + 200ml of DM water	400ml
3000cuft	300ml Perasteril + 300ml of DM water	600ml
4000cuft	400ml Perasteril + 400ml of DM water	800ml

**Recommended Dosage**

**Airborne disinfection**

7ML/M3 ( 200ML /1000CUFT): Medium contamination, High risk areas.

10ML/M3 ( 300ML /1000CUFT) : Heavy contamination, High risk areas

14ML/M3 ( 400ML /1000CUFT) : Heavy contamination, High risk areas

Dosage : 50% Dilution in DM water

**Surface Disinfection**

20% dilution of Perasteril in DM water

**Warning:**

For dilution use DM water only.  
Use of tap water will adversely affect disinfection efficacy and may clog machines nozzles.

**Application areas:**

Aseptic areas of Hospitals, Clinics, Laboratories, blood banks, Sterile area of pharmaceutical industries  
Animal houses, hatcheries, Food processing areas.

**Composition:**

Peracetic acid 0.147%  
Hydrogen peroxide 11.0%  
Purified water and acetic acid Q.S.

**Precaution:**

The concentrated product may give skin irritation.  
In case of accidental spillage wash with plenty of water.

**Storage:**

Store in cool dry area.  
Do not expose to sun light.  
Always keep container upright.

**Packing:**

6Liter X 2 carboys



**Radiant Enterprise**

[www.radiantinnovations.in](http://www.radiantinnovations.in)

C/101, 1st Floor, Shivalik Business Center, B/h, Rajpath Club, Off S. G. Highway, Bodakdev, Ahmedabad-380059. INDIA.

Phone: 91 79 40055707, 40077319

M. : 91 98250 50930, 99090 06645, 9909006620

[info@fogstarindia.com](mailto:info@fogstarindia.com), [sales@fogstarindia.com](mailto:sales@fogstarindia.com)