

# Aeros3D

Airborne Disinfectant for  
Surfaces & Environment

FORMULATION OF  
STABILIZED  
HYDROGEN PEROXIDE  
& SILVER

Broad spectrum disinfection efficacy  
**(Bactericide, Fungicide,  
Virucide, Algaecide, Sporicide)**  
on pre cleaned surfaces.



Aeros 3D is best used with airborne disinfection devices,  
which diffuses it into Hydrogen peroxide vapor.

Bio decontamination treatment of aseptic areas,  
sterile areas within 60 minutes.

Offers microbiologically validated treatment

Ecological, Odorless, Colorless

Leaves no visible residues, Biodegradable to  
non-toxic elements.

Free of Aldehydes, Quats, Chlorine

[www.radiantinnovations.in](http://www.radiantinnovations.in)

**Aeros3D+**  
Airborne disinfection devices

**SATEJ**


**SATEJ 01™**

**SATEJ PLUS™**

**TRS 01™**

**YANTRA™**

**AEROJET Steriz™**



**Highly effective &  
Automated treatment with  
diffusion time calculated as  
per room size**

### Airborne Disinfection Treatment Dosage:

Room Space	Dilution	Total solution required
1000cuft	100ml Aeros 3D + 100ml of DM water	200ml
2000cuft	200ml Aeros 3D + 200ml of DM water	400ml
3000cuft	300ml Aeros 3D + 300ml of DM water	600ml
4000cuft	400ml Aeros 3D + 400ml of DM water	800ml

### Recommended Dosage

#### Airborne disinfection

7ML/M3 (200ML/1000CUFT) : Medium contamination, High risk areas.

10ML/M3 (300ML/1000CUFT) : Heavy contamination, High risk areas

Dosage : 50% Dilution in DM water

#### Surface Disinfection

5 % dilution of Aeros3D in DM water

#### Warning:

For dilution use DM water only.  
Use of tap water will adversely affect disinfection efficacy and may clog machines nozzles.

#### Application areas:

Aseptic areas of Hospitals, Clinics, Laboratories, blood banks,

Animal houses, hatcheries, Food processing areas.

#### Composition:

Complex formulation of Stabilized Hydrogen Peroxide 11% w/v, Silver Nitrate Solution 0.01% w/v

#### Precaution:

The concentrated product may give skin irritation. In case of accidental spillage wash with plenty of water.

#### Storage:

Store in cool dry area. Do not expose to sun light. Always keep container upright.

#### Packing:

1Liter X 6 bottles  
5Liter x 2 carboys



**Radiant Enterprise**

[www.radiantinnovations.in](http://www.radiantinnovations.in)

C/101, 1st Floor, Shivalik Business Center, B/h, Rajpath Club, Off S. G. Highway, Bodakdev, Ahmedabad-380059. INDIA.

Phone: 91 79 40055707, 40077319

M. : 91 98250 50930, 99090 06645, 9909006620

[info@fogstarindia.com](mailto:info@fogstarindia.com), [sales@fogstarindia.com](mailto:sales@fogstarindia.com)